



Tel: +44 (0) 1706 869777
 E-mail: sales@desal.co.uk
 Web: www.desal.co.uk

DOWEX™ UPCORE™ Mono C-600

A Uniform Particle Size, Strong Acid Cation Exchange Resin Specifically Designed for the UPCORE System

Product	Type	Matrix	Functional group
DOWEX™ UPCORE™ Mono C-600	Strong acid cation	Styrene-DVB, gel	Sulfonic acid

Guaranteed Sales Specifications		Na ⁺ form	H ⁺ form
Total exchange capacity, min.	eq/L	2.0	1.8
	kg/ft ³ as CaCO ₃	43.7	39.3
Water content	%	42 - 48	50 - 56
Bead size distribution†			
Mean particle size	µm	585 ± 50	600 ± 50
Uniformity coefficient, max.		1.1	1.1
> 850 µm, max.	%	5	5
< 300 µm, max.	%	0.5	0.5
Whole uncracked beads, min.	%	95	95

Typical Physical and Chemical Properties		Na ⁺ form	H ⁺ form
Total swelling (Na ⁺ → H ⁺)	%	8	8
Particle density	g/mL	1.28	1.22
Shipping weight**	g/L	820	800
	lbs/ft ³	51	50

Recommended Operating Conditions

- Maximum operating temperature 120°C (250°F)
- pH range 0 - 14
- Bed depth, min. 1,200 mm (4 ft)
- Pressure drop, design max. 1.5 bar (22 psi)
- Pressure drop, max. 2.5 bar (37 psi)
- Flow rates:
 - Service/fast rinse 5 - 60 m/h (2 - 24 gpm/ft²)
 - Regeneration/displacement rinse 5 - 20 m/h (2 - 8 gpm /ft²)
- Total rinse requirement 2 - 5 Bed volumes
- Regenerant 8 - 12% NaCl, 4 - 6% HCl, or 1 - 4% H₂SO₄,

† For additional particle size information, please refer to Particle Size Distribution Cross Reference Chart (Form No. 177-01775).

** As per the backwashed and settled density of the resin, determined by ASTM D-2187.

Typical Properties and Applications

DOWEX™ UPCORE™ Mono C-600 strong acid cation exchange resin is a uniform particle size resin specifically designed for use in the UPCORE packed bed counter-current regeneration system. It is well suited for use in both demineralization and softening applications.


DOWEX UPCORE Mono C-600 resin has a smaller average particle diameter than conventional polydispersed cation resin. Its smaller, uniform size enhances operating capacity and regeneration efficiency while maintaining a moderate pressure drop.

DOWEX UPCORE Mono C-600 resin also has outstanding resistance to attrition due to compressive and osmotic stress.

Packaging

25 liter bags or 5 cubic feet fiber drums

Figure 1. Pressure Drop Data



For other temperatures use:

$$P_T = P_{20^\circ\text{C}} / (0.026 T_{\text{C}} + 0.48), \text{ where } P \equiv \text{bar/m}$$

$$P_T = P_{68^\circ\text{F}} / (0.014 T_{\text{F}} + 0.05), \text{ where } P \equiv \text{psi/ft}$$

DOWEX™ Ion Exchange Resins

For more information about DOWEX resins, call the Dow Water Solutions business:

North America: 1-800-447-4369
 Latin America: (+55) 11-5188-9222
 Europe: (+32) 3-450-2240
 Pacific: +60 3 7958 3392
 Japan: +813 5460 2100
 China: +86 21 2301 9000
<http://www.dowwatersolutions.com>

Warning: Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.

Notice: No freedom from any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other governmental enactments. Dow assumes no obligation or liability for the information in this document. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

